

ELECTRIC FILING MANICURE BITS

USE ONLY THE FOLLOWING APPROVED BITS AT THE CORRECT ROTATION SPEED

GEL REMOVAL

DEPENDING ON THE BUILDER GEL YOU HAVE TO REMOVE

ELECTRIC MANICURE

Cuticle clean Bit - MIN 3.000 - MAX 6.000 RPM - ref. 29259



6.000 RPM

Diamond Nail Prepper Cone - ref. 28564



6.000 RPM

MIN 6.000 - MAX 30.000 RPM

Tungsten Trimmer Bit - MIN 6.000 - MAX 15.000 RPM - ref. 29487



10.000 RPM 15.000 RPM

Diamond Grinder Bit - MIN 6.000 - MAX 30.000 RPM - ref. 29486




10.000 RPM 15.000 RPM

Diamond Ball Bit - MIN 6.000 - MAX 30.000 RPM - ref. 29485



10.000 RPM 15.000 RPM

Finisher Bit - MIN 6.000 - MAX 30.000 RPM - ref. 29484



6.000 RPM

NATURAL NAIL PREPARATION

Stainless Steel Tip for Sanders - ref. 30049



6.000 RPM

Green Sanders Fine 50 pcs - ref. 29916
Sanders are single use



FLEXI BUILDERS

Green Sanders Medium ref. 29917
Sanders are single use



10.000 RPM



20.000 RPM

Flexi Builder
(Clear - Pink -
Frosted Pink)

HARD BUILDERS & ALL-IN-ONE GELS



10.000 RPM



15.000 RPM

HIGH PRECISION DRILLS

MIN 6.000 - MAX 15.000 RPM

High Precision Drill Blue - ref. 28306




High Precision Drill Purple - ref. 28308



Unicorn Gel Remover Bit

MIN 10.000 - MAX 15.000 RPM - ref. 29934



SUITABLE TO REMOVE BFLEX GELS



CERAMIC BITS

MIN 6.000 - MAX 15.000 RPM

Ceramic Flame Bit Medium - ref. 29271



Ceramic Round Barrel Bit Medium Extra Long - ref. 24337

